

Crimping pliers - CRIMPFOX-RC 10 - 1212061

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for non-insulated cable lugs, 4 - 10 mm², double indent crimp

Product Features

- The CRIMPFOX-RC 10 completes the range of crimping pliers for uninsulated cable lugs and insulated tube lugs
- All pliers of this type reduce the amount of force required during crimping by 25%



Key commercial data

package_quantity	1
GTIN	4046356453936

Technical data

Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

General

Color	black
Compression	Indent crimp
Type of contact	Non-insulated cable lugs
Name	Crimping position 1
Max. cross section	4 mm ²
AWG max	12
Name	Crimping position 2
Max. cross section	6 mm ²
AWG max	10
Name	Crimping position 3
Max. cross section	10 mm ²
AWG max	8
Die station	Crimping position 4
Die station	Crimping position 5

Crimping pliers - CRIMPFOX-RC 10 - 1212061

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



accessories

Die

CRIMPFOX-RC 10/DIE - 1212062



Mounting material

Crimping pliers - CRIMPFOX-RC 10 - 1212061

accessories

CRIMPFOX/ SPR-1 - 1212069



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>