

# Screwdriver - SF-SL 0,4X2,5-75 - 1212547

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Screwdriver, slot-headed, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip

The figure shows the SZF 1 version

## Product Features

- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head
- Individually tested safety screwdrivers according to DIN EN 60900 (VDE 0682-201)
- For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC

## Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356589826

## Technical data

### Dimensions

<b>Length (b)</b>	145 mm
<b>Width (a)</b>	22 mm
<b>Blade thickness</b>	0.4 mm
<b>Blade width</b>	2.5 mm
<b>Blade height</b>	75 mm

### General

<b>Design</b>	Bladed
<b>Type</b>	Straight
<b>Material</b>	Alloyed tool steel
<b>Test standard</b>	DIN/ISO 2380-1

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	21040401
<b>eCl@ss 4.1</b>	21040401
<b>eCl@ss 5.0</b>	21040401
<b>eCl@ss 5.1</b>	21040401

# Screwdriver - SF-SL 0,4X2,5-75 - 1212547

## classifications

### eCl@ss

eCl@ss 6.0	21040401
eCl@ss 7.0	21040409
eCl@ss 8.0	21040409

### ETIM

ETIM 4.0	EC000158
ETIM 5.0	EC000158

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518


## approvals

---

GOST /

---

### Approval details



## Drawings

## Screwdriver - SF-SL 0,4X2,5-75 - 1212547

Pictogram

