

For this product we confirm RoHS-conformity

Product Code:	4S10
Distance L:	10mm
Material:	Polystyrol lightgrey
Breakdown Voltage :	50 kV/ mm
HEX:	SW9
Male thread :	M4 x 7mm
Female thread :	M4 x 7mm
Thread inserts:	Steel zinc plated
Temperature resistance:	+90°C
Minimum quantity	100pcs

