

For this product we confirm RoHS-conformity

Product Code:

4S15

Distance L:

15mm

Material:

Polystyrol lightgrey

Breakdown Voltage :

50 kV/ mm

HEX:

SW9

Male thread :

M4 x 7mm

Female thread :

M4 x 7mm

Thread inserts:

Steel zinc plated

Temperature resistance:

+90°C

Minimum quantity

100pcs

