



## NLDX2.E214025

### Motor Controllers, Magnetic - Component

[Page Bottom](#)

## Motor Controllers, Magnetic - Component

[See General Information for Motor Controllers, Magnetic - Component](#)

**TYCO ELECTRONICS AUSTRIA GMBH**

E214025

SCHRACKSTRASSE 1

3830 WAIDHOFEN/THAYA, AUSTRIA

**Magnetic motor controllers**, Cat. No. RP followed by 4 or 8 followed by 2, 4 or 6 followed by 0, 1, 7 or A, followed by 005, 006, 009, 010, 012, 021, 024, 048, 060, 110, 524, 615, 720, 730, 740, A05, A06, A09, A10, A12, A21, A24, A48, A60, B10, F05, F06, F09, F10, F12, F21, F24, F48 or F60 may be followed by up to four numbers and/or letters; Type RP920 followed by 020, 068, 123, 124, 129, 138, 139 or 145 may be followed by up to four numbers and/or letters.

Type RE followed by 0, followed by 3, followed by 0, 1, 2 or 6, followed by 005-048(5-48 vdc).

**Relays**, Type RM followed by 2, 3, 5, 6, 7, 8, C or D followed by 0, 2, 3, 7, A or B followed by 2, 3, 5, 7, 8 or 9, followed by three letters and/or numbers; may be followed by up to four letters and or numbers; Types RM900049, -900181, -900194, -900218, -900231, -900240, -900261, -900262, -900263, -900269, -900271, -900278 .

Type RY followed by 2, 3, 4, 5, 6, 7, 8 or A, followed by 1, 3 or 5, followed by 0, 1, 2, 3 or 6 followed by 003, 005, 006, 008, 009, 010, 012, 015, 018, 019, 021, 024, 026, 032, 036, 048 or 060; Types RY900068, RY900091, RY900400, RY900401, RY900402, RY900403.

**Magnetic motor controllers**, Cat. No. RT followed by 4 or E, followed by 2, 4 or 6, followed by 3, 4 or 5, followed by 002, 003, 005, 006, 009, 012, 015, 017, 018, 020, 022, 024, 28, 034, 036, 048, 052, 060, 110, 506, 512, 524, 548, 560, 615, 675, 720, 730, 740, A03, A05, A06, A09, A12, A15, A17, A18, A20, A22, A24, A34, A36, A48, A52, A60, B10, F03, F05, F06, F09, F12, F18, F24, F36 or F48, maybe followed by up to four numbers and / or letters for internal identification.

Derivative Forms: RT940009, RT940016, RT952000, RT940021, RT940022, RT940023, RT940024, RT940025, RT940026 may be followed by up to four numbers and / or letters.

Cat. No. RE followed by L, followed by 3, followed by 0, 4, 5, followed by 005, 006, 009, 012, 018, 021, 024, 036 or 048, may be followed by up to four letters and/or numbers.

Type T7N followed by S or V, followed by 1 or 5, followed by D or H, followed by 1 or 4, followed by 03, 05, 06, 09, 12, 15, 18, 24, 36 or 48, followed by WG, may be followed by up to four numbers and/or letters.

**Relays**, Type MT followed by 2, 3, 4, 7 or 8, followed by 0, 1, 2, 3, 5, A or B, followed by 0, 1, 3, 4, 5, 6, 8, 9, A, B, C, D, G, H, J, K, L, M, N, P, Q, R, S or T, followed by 006-250 (dc coils) or 006-400 (ac coils) or 0A6-2F0 (dc coils with protection diode), may be followed by up to four numbers and/or letters.

Type PE followed by 0 or 5, followed by 1 or 3, followed by 3, 4, 5 or 6, followed by 003, 005 006, 009, 012, 015, 018, 021, 024, 036, 048, A02, A03, A05, A06, A09, A12, A15, A18, A21, A24, A36, A48, C02, C03, C05, C06, C09, C12, C15, C18, C21, C24, C36, C48, F02, F03, F05, F06, F09, F12, F15, F18, F21, F24, F36, F48, H02, H03, H05, H06, H09, H12, H15, H18, H21, H24, H36 or H48, followed by up to four numbers and / or letters for manufacturer internal identification.

Type PT followed by 2, 3 or 5, followed by 2, 3, 4, 7, 8 or 9,, followed by 0 or 1, followed by three letters and/or numbers, may be followed by up to four letters and/or numbers.

**Derivative forms**, Type PT900003 may be followed by up to four numbers and/or letters.

**Magnetic motor controllers**, Type RT followed by 1, 2, 3, B, C, D, H, T or S; followed by 1, 3, 5, 7, 8, 9 or H; followed by 4, 5, C, D, K, T or L; followed by 002, 003, 005, 006, 009, 010, 012, 015, 017, 018, 020, 022, 024, 028, 034, 036, 048, 052, 060, 110, 506, 512, 524, 548, 560, 600, 615, 675, 700, 720, 730, 740, A02, A03, A05, A06, A09, A12, A15, A17, A18, A20, A22, A24, A34, A36, A48, A52, A60, B10, F03, F05, F06, F09, F12, F18, F24, F36 or F48; may be followed by up to four numbers and/or letters.

Cat. Nos. RT9H0001, RT9H0003, RT9H0004, RT9H0006, RT9H0007, RT9H0008, RT930021, RT40009, RT930023, RT930024, RT930041, RT930042, RT930043, RT930044, RT930045, RT930046, RT930039, RT930052, RT930057 may be followed by up to four numbers and/or letters.

Type RP followed by 010, 011, 030, 031, 110, 111, 130, 131, 510, 511, 530, 531, 610, 611, 630 or 631, followed by 005, 006, 009, 012, 014, 018, 020, 024, 030, 040, 048, 060 or 110; Type RP420 or RP820 followed by 005, 006, 009, 012, 021, 024, 048, 060, 110, 524, 615, 720 or 740.

Type PB, followed by 1, 3, 5, 7 or H, followed by 1 or 3, followed by 3 or 4, followed by 005 thru 048, may be followed by up to four letters and/or numbers; Types PB900001, PB900002 may be followed by up to four numbers and/or letters.

**Magnetic motor controllers**, Model LN, followed by 1, 3 or H, followed by 1 or 3, followed by 0, 3 or 4, followed by 003, 006, 009, 012, 024, 036 or 048, may be followed by up to four numbers and/or letters.

Model RX, followed by 1, 2 or 3; followed by 1, 3 or 5; followed by 4 or 5; followed by 003, 005, 006, 009, 010, 012, 015, 017, 018, 020, 022, 024, 034, 036, 048, 052, 060, 080, 110, 506, 512, 524, 548, 560, 600, 615, 675, 700 and 730; may be followed by up to four numbers and/or letters.

Model RX, followed by 4; followed by 2, 4 or 6; followed by 4 or 5; followed by 003, 005, 006, 009, 010, 012, 015, 017, 018, 020, 022, 024, 034, 036, 048, 052, 060, 080, 110, 506, 512, 524, 548, 560, 600, 615, 675, 700 and 730; may be followed by up to four numbers and/or letters.

Model RF, followed by 3, D, J or H; followed by 3, 5, 7, D, F, H or K; followed by 4 or 5; followed by 003, 005, 006, 009, 010, 012, 015, 017, 018, 020, 022, 024, 034, 036, 048, 052, 060, 080, 110, 513, 519, 531 and 537; may be followed by up to four numbers and/or letters. Derivative Forms: RF900001, RF900002 and RF900003 may be followed by up to four numbers and/or letters.

Cat. No. XT followed by 3 or 4; followed by 1, 2, 7 or 8; followed by 4 or 5; followed by 002, 003, 005, 006, 009, 010, 012, 015, 017, 018, 020, 022, 024, 028, 034, 036, 048, 052, 060, 080, 110, 506, 512, 524, 548, 615, 675, 730, L02, L03, L05, L06, L09, L10, L12, L15, L17, L18, L20, L22, L24, L28, L34, L36, L48, L52, L60, L80, M10, R06, R12, R24, R48, S15, S75, T30, LA2, LA3, LA5, LA6, LA9, LB0, LB2, LB5, LB7, LB8, LC0, LC2, LC4, LC8, LD4, LD6, LE8, LF2, LG0, LJ0, MA0, LL2, LL3, LL5, LL6, LL9, LM0, LM2, LM5, LM7, LM8, LNO, LN2, LN4, LN8, LP4, LP6, LQ8, LR2, LS0, LU0, MM0, 5L6, 5M2, 5N4, 5Q8, 6M5, 6T5 or 7P0; may be followed by up to four numbers and/or letters.

**Open type magnetic components**, Type 410 followed by 63 or 83, followed by 012, 013, 014, 016, 019, 020, 021, 022, 023, 024, 042, 043, 044, 046, 049, 050, 051, 052, 053 or 054 followed by 001, 002, 003, 005, 006, 401 or 402 or 403 followed by up to four numbers or / and letters for manufacturer internal identification. Special Type 410, followed by 63 followed by 001, 004, 008, 009, 014, 016, 022, 024, 027, or 030 followed by 000, followed by up to four numbers or / and letters for manufacturer internal identification.

**Relays**, Types WHU/F-66-H-BV1154, WSU/F-66-H-BV1155, 043016660303, 043017660604.

Type 0422-01-007-000.

Marking: Company name or "E214025" or trademarks **SCHRACK** *tyco/Electronics*, **Potter & Brumfield**, **Potter & Brumfield**, **P&B** and catalog or type designation.

Last Updated on 2007-10-09

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

Copyright © 2007 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2007 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.



**NLDX8.E214025****Motor Controllers, Magnetic Certified for Canada - Component**[Page Bottom](#)**Motor Controllers, Magnetic Certified for Canada - Component**[See General Information for Motor Controllers, Magnetic Certified for Canada - Component](#)**TYCO ELECTRONICS AUSTRIA GMBH**

E214025

SCHRACKSTRASSE 1

3830 WAIDHOFEN/THAYA, AUSTRIA

**Magnetic motor controllers**, Cat. No. RP followed by 4 or 8 followed by 2, 4 or 6 followed by 0, 1, 7 or A, followed by 005, 006, 009, 010, 012, 021, 024, 048, 060, 110, 524, 615, 720, 730, 740, A05, A06, A09, A10, A12, A21, A24, A48, A60, B10, F05, F06, F09, F10, F12, F21, F24, F48 or F60 may be followed by up to four numbers and/or letters; Type RP920 followed by 020, 068, 123, 124, 129, 138, 139 or 145 may be followed by up to four numbers and/or letters.

Type RE followed by 0, followed by 3, followed by 0, 1, 2 or 6, followed by 005-048(5-48 vdc).

**Relays**, Type RM followed by 2, 3, 5, 6, 7, 8, C or D followed by 0, 2, 3, 7, A or B followed by 2, 3, 5, 7, 8 or 9, followed by three letters and/or numbers; may be followed by up to four letters and or numbers; Types RM900049, -900181, -900194, -900218, -900231, -900240, -900261, -900262, -900263, -900269, -900271, -900278.

Type RY followed by 2, 3, 4, 5, 6, 7, 8 or A, followed by 1, 3 or 5, followed by 0, 1, 2, 3 or 6 followed by 003, 005, 006, 008, 009, 010, 012, 015, 018, 019, 021, 024, 026, 032, 036, 048 or 060 ; Types RY900068, RY900091, RY900400, RY900401, RY900402, RY900403.

**Magnetic motor controllers**, Cat. No. RT followed by 4 or E, followed by 2, 4 or 6, followed by 3, 4 or 5, followed by 002, 003, 005, 006, 009, 012, 015, 017, 018, 020, 022, 024, 28, 034, 036, 048, 052, 060, 110, 506, 512, 524, 548, 560, 600, 615, 675, 700, 720, 740, A03, A05, A06, A09, A12, A15, A17, A18, A20, A22, A24, A34, A36, A48, A52, A60, B10, F03, F05, F06, F09, F12, F18, F24, F36 or F48, maybe followed by up to four numbers and / or letters for internal identification..

Derivative Forms: RT940009, RT940016, RT952000, RT940021, RT940022, RT940023, RT940024, RT940025, RT940026 may be followed by up to four numbers and / or letters .

Cat. No. RE followed by L, followed by 3, followed by 0, 4, 5, followed by 005, 006, 009, 012, 018, 021, 024, 036 or 048, may be followed by up to four letters and/or numbers.

Type T7N followed by S or V, followed by 1 or 5, followed by D or H, followed by 1 or 4, followed by 03, 05, 06, 09, 12, 15, 18, 24, 36 or 48, followed by WG, may be followed by up to four numbers and/or letters.

**Relays**, Type MT followed by 2, 3, 4, 7 or 8, followed by 0, 1, 2, 3, 5, A or B, followed by 0, 1, 3, 4, 5, 6, 8, 9, A, B, C, D, G, H, J, K, L, M, N, P, Q, R, S or T, followed by 006-250 (dc coils) or 006-400 (ac coils) or 0A6-2F0 (dc coils with protection diode), may be followed by up to four numbers and/or letters.

Type PE followed by 0 or 5, followed by 1 or 3, followed by 3, 4, 5 or 6, followed by 003, 005 006, 009, 012, 015, 018, 021, 024, 036, 048, A02, A03, A05, A06, A09, A12, A15, A18, A21, A24, A36, A48, C02, C03, C05, C06, C09, C12, C15, C18, C21, C24, C36, C48, F02, F03, F05, F06, F09, F12, F15, F18, F21, F24, F36, F48, H02, H03, H05, H06, H09, H12, H15, H18, H21, H24, H36 or H48, followed by up to four numbers and / or letters for manufacturer internal identification.

Type PT followed by 2, 3 or 5, followed by 2, 3, 4, 7, 8 or 9, , followed by 0 or 1, followed by three letters and/or numbers, may be followed by up to four letters and/or numbers.

**Derivative forms** , Type PT900003 may be followed by up to four numbers and/or letters.

**Magnetic motor controllers**, Type RT followed by 1, 2, 3, B, C, D H, T or S; followed by 1, 3, 5, 7, 8, 9 or H; followed by 4, 5, C, D, K, T or L; followed by 002, 003, 005, 006, 009, 010, 012, 015, 017, 018, 020, 022, 024, 028, 034, 036, 048, 052, 060, 110, 506, 512, 524, 548, 560, 600, 615, 675, 700, 720, 730, 740, A02, A03, A05, A06, A09, A12, A15, A17, A18, A20, A22, A24, A34, A36, A48, A52, A60, B10, F03, F05, F06, F09, F12, F18, F24, F36 or F48; may be followed by up to four numbers and/or letters.

Cat. Nos. RT9H0001, RT9H0003, RT9H0004, RT9H0006, RT9H0007, RT9H0008, RT930021, RT40009, RT930023, RT930024, RT930041, RT930042, RT930043, RT930044, RT930045, RT930046, RT930039, RT930052, RT930057 may be followed by up to four numbers and/or letters.

Type RP followed by 010, 011, 030, 031, 110, 111, 130, 131, 510, 511, 530, 531, 610, 611, 630 or 631, followed by 005, 006, 009, 012, 014, 018, 020, 024, 030, 040, 048, 060 or 110; Type RP420 or RP820 followed by 005, 006, 009, 012, 021, 024, 048, 060, 110, 524, 615, 720 or 740.

Type PB, followed by 1, 3, 5, 7 or H, followed by 1 or 3, followed by 3 or 4, followed by 005 thru 048, may be followed by up to four letters and/or numbers; Types PB900001, PB900002 may be followed by up to four numbers and/or letters.

**Magnetic motor controllers**, Model LN, followed by 1, 3 or H, followed by 1 or 3, followed by 0, 3 or 4, followed by 003, 006, 009, 012, 024, 036 or 048, may be followed by up to four numbers and/or letters.

Model RX, followed by 1, 2 or 3; followed by 1, 3 or 5; followed by 4 or 5; followed by 003, 005, 006, 009, 010, 012, 015, 017, 018, 020, 022, 024, 034, 036, 048, 052, 060, 080, 110, 506, 512, 524, 548, 560, 600, 615, 675, 700 and 730; may be followed by up to four numbers and/or letters.

Model RX, followed by 4; followed by 2, 4 or 6; followed by 4 or 5; followed by 003, 005, 006, 009, 010, 012, 015, 017, 018, 020, 022, 024, 034, 036, 048, 052, 060, 080, 110, 506, 512, 524, 548, 560, 600, 615, 675, 700 and 730; may be followed by up to four numbers and/or letters.

Model RF, followed by 3, D, J or H; followed by 3, 5, 7, D, F, H or K; followed by 4 or 5; followed by 003, 005, 006, 009, 010, 012, 015, 017, 018, 020, 022, 024, 034, 036, 048, 052, 060, 080, 110, 513, 519, 531 and 537; may be followed by up to four numbers and/or letters. Derivative Forms: RF900001, RF900002 and RF900003 may be followed by up to four numbers and/or letters.

Cat. No. XT followed by 3 or 4; followed by 1, 2, 7 or 8; followed by 4 or 5; followed by 002, 003, 005, 006, 009, 010, 012, 015, 017, 018, 020, 022, 024, 028, 034, 036, 048, 052, 060, 080, 110, 506, 512, 524, 548, 615, 675, 730, L02, L03, L05, L06, L09, L10, L12, L15, L17, L18, L20, L22, L24, L28, L34, L36, L48, L52, L60, L80, M10, R06, R12, R24, R48, S15, S75, T30, LA2, LA3, LA5, LA6, LA9, LB0, LB2, LB5, LB7, LB8, LC0, LC2, LC4, LC8, LD4, LD6, LE8, LF2, LG0, LJ0, MA0, LL2, LL3, LL5, LL6, LL9, LM0, LM2, LM5, LM7, LM8, LN0, LN2, LN4, LN8, LP4, LP6, LQ8, LR2, LS0, LU0, MM0, 5L6, 5M2, 5N4, 5Q8, 6M5, 6T5 or 7P0; may be followed by up to four numbers and/or letters.

**Relays**, Types WHU/F-66-H-BV1154, WSU/F-66-H-BV1155.

Type 410 followed by 63 or 83, followed by 012, 013, 014, 016, 019, 020, 021, 022, 023, 024, 042, 043, 044, 046, 049, 050, 051, 052, 053 or 054, followed by 001, 002, 003, 005, 006, 401 or 402 or 403; followed by up to four numbers or/and letters for manufacturer internal identification. Special Type 410, followed by 63 followed by 001, 004, 008, 009, 014, 016, 022, 024, 027 or 030 followed by 000, followed by up to four numbers or / and letters for manufacturer internal identification.

**Relays**, Types WHU/F-66-H-BV1154, WSU/F-66-H-BV1155, 043016660303, 043017660604.

Type 04090608 followed by 3000, 4000, 5000 or 7000.



Marking: Company name or "E214025" or trademarks



, catalog or type designation, and the Recognized Component

Mark for Canada, .  
Last Updated on 2007-10-09

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

Copyright © 2007 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2007 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

