

Partner für Sensorik

Your Sensor Partner

technical data

19.01.2012

slot type switch
AC/DC 3-wire
60 x 30 x 45mm

ident-no.:
75687_CO
type:
Conrad-Typ: 505371

revision index: 000

output change over

switching capacity max. 20 W/VA

switching voltage 150 V AC/DC

switching current max. 1000 mA

switch on time 2,5 ms

switch off time 2,5 ms

switching frequency max. 100 Hz

lifetime at nominal load 10 ⁵ to 10 ⁶ operations

operating temperature range -25°C ... +80°C

degree of protection acc. to DIN 60 529 IP67

dielectric test voltage ac (rms.) Ui

on/off indication - - -

housing material plastics


connection 1m PVC-cable


3 x 0.34mm²


Reed switches are not suitable for direct switching of lighting, power supplies, drives, etc.

(the max current often exceeded during startup/when off).

Additional coupling with protective relays use.







				•	
Schutzvermerk nach		(Zul.Abw.) Oberfläche	Maßstab 1:1	(Gewicht)
		Allgemeint	ol. nach DIN	(Werkstoff,Halbzeug) (Rohteil-Nr.)	
DIN 34 beachten		nach DIN ISO 2768	-m 3141	(Rohteil-Nr,) (Modell-oder Gesenk-Nr.)	1
		2012 Datu	m Name	(Benennung)	·
		Bearb. 17.0	1. Seifer	1,	
		Gepr.		Reed-Magn	ietschalter
			Secatec electronic GmbH	60x45x30mm	Umschalter
		R D	nappenstraße 154 -57581 Katzwinkel	(Zeichnungsnummer)	Blatt
		(0	049)02741/9460-0	75687 CO	
**			www.secatec.de		BI,
Änderungsindex	Datum Nam	e(Urspr.)		(Ers.f,:)	(Ers.d.;)