

**RIDERSERIES
SRC-I QV S**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Cross-connector for bridging connections in the
RIDERSERIES RC1

General ordering data

Type	SRC-I QV S
Order No.	1132070000
Version	RIDERSERIES, Cross-connector, No. of contacts: 8, Continuous current: 12 A
GTIN (EAN)	4032248912087
Qty.	10 pc(s).

Datenblatt

**RIDERSERIES
SRC-I QV S**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Width	11 mm	Net weight	6.7 g
-------	-------	------------	-------

Temperatures

Operating temperature	-40 °C...+85 °C	Storage temperature	-40 °C...+85 °C
-----------------------	-----------------	---------------------	-----------------

Input

Coil resistance	Pull-inrop-out current, typ.
Pull-inrop-out typ.	

Output

Continuous current	12 A
--------------------	------

Contact data

No. of contacts	8
-----------------	---


Insulation coordination

Protection degree	IP 20
-------------------	-------

Classifications

eClass 6.2	27-14-11-40	eClass 7.1	27-37-16-03
------------	-------------	------------	-------------

Approvals

Approvals	
ROHS	Conform