

Technical datasheet: KPUS-40T-16T-K768

Specifications:

Operating Temperature Range	-30°C to +80°C
Storage Temperature Range	-40°C to +85°C
Center Frequency	40±1 KHz
Capacitance at 1 KHz	2100± 20% pF
Sound Pressure Lever	≥ 117dB at 40KHz, 30cm, 10Vrms
Directivity	55° (typ.)
Max. Input Voltage	20Vp-p at 40KHz Square wave
Insulation Resistance	100MΩ Min at 50V DC
Housing Material	Aluminum

Dimensions:

