

Technical datasheet: KPUS-40T-16R-K769

Specifications:

Operating Temperature Range	-30°C to +80°C
Storage Temperature Range	-40°C to +85°C
Center Frequency	40±1 KHz
Capacitance at 1 KHz	2100± 20% pF
Sensitivity	≥-67dB at 40KHz, 30cm (0dB=10V/Pa)
Directivity	55° (typ.)
Insulation Resistance	100MΩ Min at 50V DC
Housing Material	Aluminum

Dimensions:

