

# Power module - EMD-SL-PS-110AC - 2866116

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Power modules, pluggable, for EMD-SL-..., supply voltage: 88...121 V AC

## Product Features

- Separately adjustable startup and response delays
- Variable supply voltage range
- Adjustable via potentiometer on the front

## Key commercial data

package_quantity	1
GTIN	4017918952686

## Technical data

### Dimensions

Width	32 mm
Height	35 mm
Depth	16 mm

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

### Input data

Nominal input voltage	110 V AC (50/60 Hz)
Input voltage range AC	88 V AC ... 121 V AC

## classifications

### eCl@ss

eCl@ss 4.0	27371105
eCl@ss 4.1	27371105
eCl@ss 5.0	27049090
eCl@ss 5.1	27049201
eCl@ss 6.0	27049201
eCl@ss 7.0	27049201
eCl@ss 8.0	27049201

## Power module - EMD-SL-PS-110AC - 2866116

### classifications

#### ETIM

<b>ETIM 2.0</b>	EC001438
<b>ETIM 3.0</b>	EC001438
<b>ETIM 4.0</b>	EC001438
<b>ETIM 5.0</b>	EC001438

#### UNSPSC

<b>UNSPSC 6.01</b>	30211916
<b>UNSPSC 7.0901</b>	39121535
<b>UNSPSC 11</b>	39121535
<b>UNSPSC 12.01</b>	39121535
<b>UNSPSC 13.2</b>	39121535

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>