



NO.	DESCRIPTION	SPECIFICATION	UNIT	Q' TY
1	COPPER TUBE	Ø2.0mm针仔(M490, M492) 镀镍	EA	2
2	PLUG	Ø0.60×7.40×30±0.5mm black color hardware.Ni-plete (Ø0.60×7.40×30±0.5mm黑色五金, 镀镍)	EA	1
3	PLUG HOLDER	Used 30P black PVC Color. (30P黑色PVC胶料)	EA	1
4	RESISTANCE	IC2501 90W. (IC2501 90W)	EA	1

MODEL : VAS-4200-A0

TOLERANCE	DESIGN/DATE	兰宗洲11/08/2008	DP PLUG	END-05692			
	DRAWING/DATE	兰宗洲11/08/2008		K-tip-V3 IC2501 (90W)	DESIGN	SIGN	REV
X=±0.5mm	ASSESSOR		00			R0	
. X=±0.3mm	DATE						
. XX=±0.05mm	RATIFIER			MM			
	DATE						