

# Current transformer - PACT MCR-V2-3015- 60- 60-5A-1 - 2277815

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Window-type current transformer, 60 A AC primary current; 5 A AC secondary current; accuracy class 1; 1.25 VA rated power

## Key commercial data

package_quantity	1
GTIN	4046356502160

## Technical data

### Dimensions

Primary round conductor (diameter)	28 mm
Primary round conductor (width)	30 mm
Primary round conductor (height)	15 mm
Primary round conductor (width)	20 mm
Primary round conductor (height)	20 mm
Width	30 mm
Height	80 mm
Depth	60 mm
Width with alternative assembly	60 mm
Height with alternative assembly	80 mm
Depth with alternative assembly	30 mm

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 40 °C
Ambient temperature (storage/transport)	-25 °C ... 40 °C

### Input data

Thermal rated short-time current	$I_{th} = 60 * I_n$
Rated surge current	$I_{dyn} = 2.5 * I_{th}$
Rated frequency: Standard converter	50 Hz ... 60 Hz
Surge current limitation factor	FS 5
Rated power	1.25 VA
Primary rated current $I_{pn}$	0 A ... 60 A
Secondary rated current $I_{sn}$	5 A AC

## General

# Current transformer - PACT MCR-V2-3015- 60- 60-5A-1 - 2277815

## Technical data

### General

<b>Converter type</b>	Plug-on converters
<b>Class</b>	1
<b>Can be calibrated</b>	No
<b>Rated insulation voltage</b>	1 kV
<b>Test voltage input/output</b>	3 kV (50 Hz, 1 min.)
<b>Standards/regulations</b>	IEC 60044-1
<b>Color</b>	black
<b>Housing material</b>	Polyamide PA fiberglass reinforced

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27210902
<b>eCl@ss 4.1</b>	27210902
<b>eCl@ss 5.0</b>	27210902
<b>eCl@ss 5.1</b>	27210902
<b>eCl@ss 6.0</b>	27210902
<b>eCl@ss 7.0</b>	27210902
<b>eCl@ss 8.0</b>	27210902

### ETIM

<b>ETIM 2.0</b>	EC001505
<b>ETIM 3.0</b>	EC001505
<b>ETIM 4.0</b>	EC002048
<b>ETIM 5.0</b>	EC002048

### UNSPSC

<b>UNSPSC 6.01</b>	30211501
<b>UNSPSC 7.0901</b>	39121019
<b>UNSPSC 11</b>	39121006
<b>UNSPSC 12.01</b>	39121006
<b>UNSPSC 13.2</b>	39121006

## accessories

### Mounting material

PACT-FAST-MNT-W16-L65 - 2276641



# Current transformer - PACT MCR-V2-3015- 60- 60-5A-1 - 2277815

accessories

PACT-FAST-MNT-W16-L40 - 2276638



## Drawings

Dimensioned drawing

