

Mounting material - PACT-FAST-MNT-W16-L65 - 2276641

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



The transformer quick-action mechanism enables the lightning-fast mounting of PACT current transformers on the power rail. The installation can be completed easily by hand without the use of tools. Fixing pins: 65 mm, holding latches: 16 mm

Key commercial data

package_quantity	1
GTIN	4046356659017

Technical data

Dimensions

Width	16 mm
Depth	65 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 120 °C
--	-------------------

General

Housing material	PA 6
Torque	0.4 Nm
Note	The 16 mm wide converter attachment can also be used for larger current transformers if the length of the fixing pins is sufficient.

classifications

eCl@ss

eCl@ss 4.0	27210902
eCl@ss 4.1	27210902
eCl@ss 5.0	27210902
eCl@ss 5.1	27210902
eCl@ss 6.0	27210902
eCl@ss 7.0	27210902
eCl@ss 8.0	27210902

ETIM

ETIM 3.0	EC001505
ETIM 4.0	EC002048
ETIM 5.0	EC002615

Mounting material - PACT-FAST-MNT-W16-L65 - 2276641

classifications

UNSPSC

UNSPSC 6.01	30211501
UNSPSC 7.0901	39121019
UNSPSC 11	39121006
UNSPSC 12.01	39121006
UNSPSC 13.2	39121006

Drawings

Dimensioned drawing

