

Current transformer - PACT MCR-V2-5012- 85-800-5A-1 - 2277187

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Window-type current transformer, 800 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

Key commercial data

package_quantity	1
GTIN	4046356305044

Technical data

Dimensions

Primary round conductor (diameter)	42 mm
Primary round conductor (width)	50 mm
Primary round conductor (height)	12 mm
Note on dimensions	2
Primary round conductor (width)	40 mm
Primary round conductor (height)	10 mm
Width	30 mm
Height	108 mm
Depth	85 mm
Width with alternative assembly	85 mm
Height with alternative assembly	108 mm
Depth with alternative assembly	30 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 40 °C
Ambient temperature (storage/transport)	-25 °C ... 40 °C

Input data

Thermal rated short-time current	$I_{th} = 60 * I_n$
Rated surge current	$I_{dyn} = 2.5 * I_{th}$
Rated frequency: Standard converter	50 Hz ... 60 Hz
Surge current limitation factor	FS 5
Rated power	10 VA
Primary rated current I_{pn}	0 A ... 800 A

Current transformer - PACT MCR-V2-5012- 85-800-5A-1 - 2277187

Technical data

Input data

Secondary rated current I_{sn}	5 A AC
--	--------

General

Converter type	Plug-on converters
Class	1
Can be calibrated	No
Rated insulation voltage	1 kV
Test voltage input/output	3 kV (50 Hz, 1 min.)
Standards/regulations	IEC 60044-1
Color	black
Housing material	Polyamide PA fiberglass reinforced

classifications

eCl@ss

eCl@ss 4.0	27210902
eCl@ss 4.1	27210902
eCl@ss 5.0	27210902
eCl@ss 5.1	27210902
eCl@ss 6.0	27210902
eCl@ss 7.0	27210902
eCl@ss 8.0	27210902

ETIM

ETIM 2.0	EC001505
ETIM 3.0	EC001505
ETIM 4.0	EC002048
ETIM 5.0	EC002048

UNSPSC

UNSPSC 6.01	30211501
UNSPSC 7.0901	39121019
UNSPSC 11	39121006
UNSPSC 12.01	39121006
UNSPSC 13.2	39121006

accessories

Mounting material

Current transformer - PACT MCR-V2-5012- 85-800-5A-1 - 2277187

accessories

PACT-FAST-MNT-W13-L65 - 2276625



PACT-FAST-MNT-W13-L40 - 2276612



Drawings

Dimensioned drawing

