

SPECIFICATION

1. Input:

1.1 Input Voltage:	5V DC
1.2 Input Current:	---
1.3 Protection:	---
1.4 Input Inlet:	With 4 changeable output plugs (4PPM)

2. Output:

2.1 Output Voltage:	5V DC
2.2 Output Current:	1000mA
2.3 Protection:	---

3. Environmental Requirements

3.1 Operating Temperature:	0°C To 35°C
3.2 Storage Temperature:	-20°C To 60°C
3.3 Operating Humidity:	20%-85% Rh Non-Condensing
3.4 Storage Humidity:	10%-90% Rh Non-Condensing

4. Cable Length: 1M

5. With 4 output plugs:

- (1) Female USB
- (2) Nokia 2,0 mm
- (3) Mini USB
- (4) Micro USB

6. Device Colour: Black

7: Weight

CB8 Cable: 27g

Nokia 2,0 mm plug: 3g

Mini USB plug : 4g

Micro USB plug: 4g

Female USB plug: 8g

8. Mechanical Specification: Consult Attached Drawing

