

For All Industries Require Professional Flash Inspection, Data Pre-load, and Sanitization

Intelligent 9 Standard/Golden Series CF Duplicator

- ✧ 3.9GB/min copy speed
- ✧ Data & System Copy
- ✧ Bit-by-bit Inspection for Bad Sector/ Reading & Writing Speed / Real Capacity
- ✧ Quick Erase & DoD Erase
- ✧ Burn-in test (for Golden Series)
- ✧ Anti-tampering Log Report (for Golden Series)



Function & Features

Copy Performance

- ✧ Two modes of operation: Standalone or PC-link
- ✧ Impeccable copy speed: up to 3.9GB per min for each port and up to 120 ports.
- ✧ High Compatibility: Support Data & System Copy with Linux(ext2/3/4), NTFS, FAT16/32/64.
Support all formats while doing whole media copy.

Diagnostic & Erase

- ✧ H5 Test: bit-by-bit Inspection for Bad Sector/ Reading & Writing Speed / Real Capacity
- ✧ H6 Test: to skip data area without losing data of flash while inspecting quality.
- ✧ Three erase method: Quick Erase, Full Erase, DoD Erase

Advanced Functions

- ✧ Burn-In test: User can set how long and how many loops the Burn-In test last. It ranges from 30 minutes to 30 days. (for Golden Series)
- ✧ Anti-Tampering Log Report: (for Golden Series)
 - Any falsification can be detected to ensure report is genuine.
- ✧ PC-link connection (for Golden Series):
 - Real-Time Monitoring & Controlling multi-duplicator via PC screen with better efficiency
 - Real-Time recording and viewing the log report

Maintenance

- ✧ Easy Maintenance: Quick Swap module helps to reduce maintenance cost.

Ergonomic

- ✧ Special guiding design helps to make flash insertion and removal easier.

Specification

Photo									
CF Model	CF904	CF908	CF916	CF924	CF932	CF940	CF960	CF980	CF9120
Targets	1:3	1:7	1:15	1:23	1:31	1:39	1:59	1:79	1:119
Specification	Buffer	128MB							
	Maximum Speed Supported	3.9GB/min							
	Capacity	Up to 2TB							
	Operating Type	➤ Support PC link for monitoring and event log report output							
		➤ Stand alone operation							
	Language Support	English, Japanese							
	Display	Monochrome LCD Display							
	Status LED	LED(Red/Green) on each slot							
Control Button	4 push buttons(▲, ▼, OK, ESC)								
Function	Copy Function	Quick Copy (Systems & Files Copy)							
		Whole Media Copy							
		Asynchronous Duplication							
		Copy up to 119 targets							
	Compare Function	Bit by Bit data comparison							
	Diagnostic Function	Speed Test; Capacity Test; A2 Fake Card Test							
		H3 Test: Read only							
		H5 Test: Read & Write							
Erase Function	Quick Erase; Full Erase; DoD Erase								
Format Function	FAT16/32 Format								

Advanced Function (for Golden Series)	Use Port 2 as Compare Source	To prevent copy fail caused by worm source
	Log Manager	Record Log Report
		Anti-Tampering Log Report
	PC-Link	Real Time PC Monitoring
Burn-in Test	Ranges from 30 mins to 30 days	
Compatibility	Flash Devices Compatible	CF Type I. CF1.0, CF2.0, CF3.0, CF4.0, CF4.14
	Format Supported	Quick Copy: FAT16/32/64, NTFS, Linux(Ext2/Ext3/Ext4)
		Whole Media Copy: All Formats
Operation system supported	All (Windows, Linux, Other stand-alone systems)	
Hardware Specification	Power Supply	12V Adapter
	Working Temperature	5°C ~ 45°C
	Storage Temperature	-20°C ~85°C
	Working Humidity	20% ~ 80%
	Storage Humidity	5% ~ 95%
	Dimension (cm)	From 24.1x19.5x11.5 to 45x30x29.5
	Weight (kg)	From 1.9 to 19
Certification	FCC, CE, RoHS	