



Sample photo

Order symbol: PCM 150/125 G
Product nbr: 6016316
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074038104
EI. number:
 Finland 3421643
 Denmark 8212027200
 Italy 7341055
 Sweden 2535333

Including: Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:		L	W	H	Rating:
mm:		180	130	125	Ingress Protection (EN 60529): IP 66/67
inch:		7.1	5.1	4.9	Impact Resistance (EN 50102): IK 08
Materials:					
Material:		PC			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Gasket material:		TPE			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MIV 150		Mounting plate			
MIN 10		DIN-15 Mounting rail			
MIN 15		DIN-15 Mounting rail			
MIV 10		DIN-35 Mounting rail			
MIV 15		DIN-35 Mounting rail			
FP A 150/180		Front plate			
HFP 180		Front plate hinge series			
					Certificates:
					Germanischer Lloyd (GL)
					Underwriters Laboratories
					Det Norske Veritas
					Fimko
					Europe EN 50298 1998
					UL Canada
					Gost R

