



Sample photo

Order symbol: PCM 175/75 T
Product nbr: 6016920
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074024510
El. number:
 Finland 3422262
 Denmark 8212027433
 Sweden 2535437

Including: Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:			L		W		H		Rating:	
mm:	180	180	75					Ingress Protection (EN 60529): IP 66/67		
inch:	7.1	7.1	3					Impact Resistance (EN 50102): IK 08		
Materials:										
Material:	PC									
Base colour:	RAL 7035									
Cover colour:	Smoked grey									
Cover screws material:	Polyamide									
Cover screws colour:	Black									
Gasket material:	TPE									
Temperatures:										
Short term:	-40 ... 120 °C									
Continuous:	-40 ... 80 °C									
Short term:	-40 ... 250 °F									
Continuous:	-40 ... 175 °F									
Accessories:										
MIV 175	Mounting plate									
MIN 15	DIN-15 Mounting rail									
MIV 15	DIN-35 Mounting rail									
FP A 175/180	Front plate									
HFP 180	Front plate hinge series									
Certificates:										
Germanischer Lloyd (GL)										
Underwriters Laboratories										
Det Norske Veritas										
Fimko										
Europe EN 50298 1998										
UL Canada										
Gost R										

