



Sample photo

**Order symbol:** PCM 175/150 T  
**Product nbr:** 6016923  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**EAN:** 6418074052285  
**EI. number:**  
 Finland 3435222  
 Denmark 8212027556  
 Sweden 2535441

**Including:** Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:		L	W	H	Rating:
mm:		180	180	150	<b>Ingress Protection (EN 60529):</b> IP 66/67
inch:		7.1	7.1	5.9	<b>Impact Resistance (EN 50102):</b> IK 08
Materials:					
<b>Material:</b>		PC			
<b>Base colour:</b>		RAL 7035			
<b>Cover colour:</b>		Smoked grey			
<b>Cover screws material:</b>		Polyamide			
<b>Cover screws colour:</b>		Black			
<b>Gasket material:</b>		TPE			
Temperatures:					
<b>Short term:</b>		-40 ... 120 °C			
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
Accessories:					
MIV 175		Mounting plate			
MIN 15		DIN-15 Mounting rail			
MIV 15		DIN-35 Mounting rail			
FP A 175/180		Front plate			
HFP 180		Front plate hinge series			
Certificates:					
		Germanischer Lloyd (GL)			
		Underwriters Laboratories			
		Det Norske Veritas			
		Fimko			
		Europe EN 50298 1998			
		UL Canada			
		Gost R			

