


4-CONDUCTOR DEVICE CONNECTORS FOR FIXING SCREW AND NUT 3 MM Ø OR FOR SELF TAPPING SREW 2.9 MM Ø FROM TOP


PDF DATASHEET

© 1992 - 2011 CADENAS GmbH











4-CONDUCTOR DEVICE CONNECTORS FOR FIXING SCREW AND NUT 3 MM Ø OR FOR SELF TAPPING SREW 2.9 MM Ø FROM TOP 2 POLE

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

862-552 TO 862-2652

ITEM-NO. (ITEM-NO.)	862-1552
Cross section1 (Cross section / mm²)	0.5 - 4
Cross section2 (Cross section / AWG)	20 - 12
Strip length (Strip length / mm)	10 - 11
Measured voltage (Measured voltage / V)	500
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	32
P (NO. OF POLES)	2
Height (Height / mm)	21.4
Width (Width / mm)	24
Depth (Depth / mm)	35
No. of connection Points (No. of connection Points)	8
No. of potentials (No. of potentials)	2
COLOR (COLOR)	schwarz
Comment (Comment)	L1-N