







Rating	8A 125V/250V AC 	Mounting Hole
Contact Resistance	DC 500V 100M ohm Min.	
Insulation Resistance	AC 1500V 1 minute	
Fuse Size	ø5.0*20mm	

Material:
Frame: Black, PBT
Terminals: Nickel Plated Brass



Tolerances ±0.3 Unless Otherwise Specified

							△
							△
Date	Name	Description				No.	
Drawn	Checked	Approved	SCI BOM No.	1310264	Model Name	FUSE HOLDER	
柳新強			Customer No.		Model No.	R3-45A	
02/03/15			Unit	mm		Rev. X0	