



Data



Electrical data

Ratings per IEC/EN 60664-1

Rated voltage (II / 2)	400 V
Rated impulse voltage (II / 2)	4 kV
Rated current	24 A
Legend (ratings)	(II / 2) Δ Overvoltage category II / Pollution degree 2

Connection data

Connection technology	CAGE CLAMP®
Actuation type	Push-in
Connectable conductor materials	Copper
Solid conductor	0.5 ... 2.5 mm ² / 20 ... 16 AWG
Fine-stranded conductor	0.5 ... 2.5 mm ² / 20 ... 16 AWG
Strip length	9 ... 11 mm / 0.35 ... 0.43 Inch
Total number of connection points	2
Total number of potentials	1
Type of wiring	Side-entry wiring

Geometrical Data

Width	8 mm / 0.315 inch
Height	15.5 mm / 0.61 inch
Depth	42 mm / 1.654 inch

Material Data

Color	gray
Fire load	0.099 MJ
Weight	5 g

Commercial data

Country of origin	CH
GTIN	4044918818407
Customs Tariff No.	85369010000

Approvals / Certificates

Country specific Approvals

Logo	Approval	Certificate name
	CSA DEKRA Certification B.V.	1053495



VDE
VDE Prüf- und Zertifizierungsinstitut

40022792



Ship Approvals

Logo

Approval

Certificate name

ABS

ABS
American Bureau of Shipping

15-HG1419918-PDA

BV

BV
Bureau Veritas S.A.

11914/C0 BV



DNV GL
Det Norske Veritas, Germanischer Lloyd

TAE000015T

UL-Approvals

Logo

Approval

Certificate name

CCA

UL
UL International Germany GmbH

CCA-DK No. 2527



UL
UL International Germany GmbH

E69654

Compatible products

General accessories



Item no.: 249-130
Syringe; Contents: 20 ml Alu-Plus contact paste

www.wago.com/249-130

Downloads

Documentation

Bid Text

224-201



Oct 10, 2017

DOC
25.6 kB

Download

smartDATA

CAD data

3D Download 224-201

URL

Download

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.