

## Product Description

High degree of protection; For the smallest conductor sizes; Low height; Gentle cable clamping; High packing density



## Application range

- For use wherever there is limited assembly space.
- Sensors
- Measuring technology

## Benefits

- High degree of protection
- For the smallest conductor sizes
- Low height
- Gentle cable clamping
- High packing density



Technical Data

Material

Body: nickel-plated brass Seal: CR/NBR

Temperature range

-20°C to +100°C

Protection rating

IP 68

Article List

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINDICHT® MINI						
52001860	MINI 6 x 1	2 - 3	9	19,5	5.0	50
52001880	MINI 8 x 1	3,5 - 5,5	11	20,5	5.0	50

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.