



DATA SHEET	52103000
SKINDICHT® SM-M	valid from : 19.10.2009

SKINDICHT® is a hexagonal brass counter nut with metric thread in according to DIN EN 50262.

Counter brass nuts are required in cases if glands have to be countered or thin housings allow only through borings.



Technical feature:

Connecting thread: M 12x1.5 up to M 110x2 in acc. to EN 60423

Material: Nickel plated brass

Part number	Type Size M	Wrench size mm	Thickness mm	Outer Ø
5210 3000	SKINDICHT SM-M 12x1,5	15	3	16,5
5210 3010	SKINDICHT SM-M 16x1,5	19	3	20,9
5210 3020	SKINDICHT SM-M 20x1,5	24	3,5	26,4
5210 3030	SKINDICHT SM-M 25x1,5	30	4	33
5210 3040	SKINDICHT SM-M 32x1,5	36	4	39,6
5210 3050	SKINDICHT SM-M 40x1,5	46	5	50,6
5210 3060	SKINDICHT SM-M 50x1,5	60	5	66
5210 3070	SKINDICHT SM-M 63x1,5	70	5	77
5210 3071	SKINDICHT SM-M 75x1,5	85	8	95
5210 3072	SKINDICHT SM-M 90x2	102	10	114
5210 3073	SKINDICHT SM-M 110x2	124	12	135

For more information please see our current catalogue.

Please do not hesitate to contact our laboratory if there any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: M. Steinberg	Document: DB52103000_1EN	page 1 of 1
---------------------------------------	--------------------------	-------------