


A B C D E F G H

1
2
3
4
5
6



Model No.	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)
GM-0503	8	5	3	4.5	1.5
GM-0603	8.5	6	3	4.7	1.7
GM-0705	10.2	7.2	5	4.4	1.7
GM-0804	11	8	4	5	1
GM-0805	11	8	5	5.5	1.5
GM-0806	12	8	6	5.5	1.5
GM-1006	13.3	10	6.4	6.3	1.7
GM-1108	15.5	11	7.8	9	3
GM-1408	18	14	8	6	1
GM-1410	19.5	13.9	10.5	6.4	3.4
GM-1812	22	18	12	8	1
GM-2015	23.7	20.1	15.5	6.1	1.7
GM-2518	29.9	25.1	18.9	7.2	1.5
GM-3225	38.1	31.7	25	7.8	1.5

MATERIAL : Soft PVC
 HARDNESS : 45 - 50 shore A
 WORKING TEMP. : -20 ~ 80°C
 COLOR : Black
 TOLERANCE : ±0.5

DATE	REVISION	APPROVAL BY

DIMENSION	mm
DRAW BY	Camily
APPROVAL BY	Rikki
DATE	03-12-08

NAME SOFT PVC GROMMET