

Product Description

For fixed applications;High tensile strength;Space-saving



Application range

- In combination with protective conduit
- SILVYN® LCC-2
- SILVYN® LCCH-2
- Outdoors
- Applications with high mechanical stress

Benefits

- For fixed applications
- High tensile strength
- Space-saving

Design

- Metric connection thread
- Hexagonal collar
- Cap nut



Technical Data

Material

Nickel-plated brass

Protection rating

IP 54

Article List

Part number	Article designation	Overall length/ C (mm)	Thread length/ D (mm)	SW (mm)	Suitable for SILVYN® LCC-2/LCCH-1	Pieces / PU
SILVYN® LGF-2-M						
55501981	12 x 1,5	21.0	8.0	13	10	10
55502001	16 x 1,5/1	23.0	8.0	17	12	10
55502002	16 x 1,5/2	25.0	10.0	20	16	10
55502021	20 x 1,5/1	25.0	10.0	22	16	10
55502022	20 x 1,5/2	26.3	10.0	24	20	10
55502031	25 x 1,5	32.5	10.0	29	25	10
55502041	32 x 1,5	36.8	13.0	38	32	10
55502051	40 x 1,5	39.0	14.0	48	40	4
55502061	50 x 1,5	42.0	15.0	58	50	4
55502071	63 x 1,5	50.0	18.0	70	63	1

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.