



DATA SHEET	53015600
SKINTOP BS / BSR[®]	valid from : 04.09.2006

SKINTOP[®] BS / BSR with polyamide spiral strain relief, is particularly used for flexible cables a handheld equipment, moving machine parts and in many applications of the instrument industry.
Skintop BS / BSR with spiral afford protection against conductor damage.



The gland component parts:

Gland body with lamellar design
Cap nut with spiral
Seal insert

plastic polyamide-based (UL94-V2)
plastic polyamide-based (UL94-V2)
elastomere

Technical features:

Connecting thread:
Functional thread:
IP protection:
Strain relief:
Temperature range:
Type:

PG 7 up to PG 21 in acc. to DIN 40 430
multi-start trapezoidal thread
IP 68 - 5 bar, test in acc. to EN 60 529
in acc. to DIN VDE 0619
- 20°C up to + 80°C
BS = standard;
BSR = standard with reducing seal insert

Approval:



For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: R. Drotleff	Document: DB53015600_2EN	page 1 of 1
--------------------------------------	--------------------------	-------------