


SKINTOP® BT Valid: 07.02.2012

Product Description

Reliable bending and anti-kink protection; Cable conservation; Functional reliability





Application range

- Cables for electrical appliances and machinery that are moved under normal use must be protected against excessive bending as required in accordance with VDE 0730.
- · Handheld device
- Apparatus construction
- Light and sound applications
- Moving machine parts

Benefits

- · Reliable bending and anti-kink protection
- · Cable conservation
- · Functional reliability

Design

PG connection thread

Note

- Refer to SKINTOP® PG accessories for suitable accessories
- Counter nut to be used: SKINTOP® GMP-GL



Product Information

Page 2 of 2

SKINTOP® BT Valid: 07.02.2012

Technical Data

Caution

Refer to Appendix T21 for the installation dimensions and torques

Colour delivered

Silver grey (RAL 7001)

Material

Body: Polyamide Seal: CR

Protection rating

IP 68 - 5 bar

Temperature range

-20°C to +80°C

Article List

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINTOP® BT silver grey						
53015410	9	3,5 - 8	19	42,9	8.0	100
53015420	11	4 - 10	22	47,7	8.0	100
53015430	13,5	5 - 12	24	52.0	9.0	50
53015440	16	9 - 14	27	55,9	10.0	50
53015450	21	13 - 18	33	64,4	11.0	50

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.