



<b>DATA SHEET</b>	52015700
<b>SKINTOP® MS / MSR</b>	valid from : 04.09.2006

The SKINTOP® MS / MSR, a nickel-plated brass cable gland which combines high quality with regard to consistency and reliability, is especially designed for use in manufacturing of machines and equipment, in measuring, controlling as well as in the pharmaceutical industry and for medical equipment.



**The gland make-up consists of:**

Gland body with lamellar design	nickel-plated brass
Cap nut	nickel-plated brass
Insert with lamellar design	plastic polyamide-based
Seal insert	elastomere
Sealing ring	elastomere

**Technical features:**

Connecting thread:	PG 7 up to PG 48 in acc. to DIN 40 430
Functional thread:	PG 7 up to PG 48 in acc. to DIN 40430
IP protection:	IP 68 - 5 bar, test in acc. to EN 60 529
Temperature range:	- 25°C up to + 100°C
Type:	MS = standard; MSR = standard with reducing seal insert

**Recommended torque rates in acc. to DIN VDE 0619**

PG 7 – PG 13.5	6.25 Nm
PG 16	7.5 Nm
PG 21 – 48	10.0 Nm

For more information please see our current catalogue.  
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: R. Drotleff	Document: DB52015700_1EN	page 1 of 1
--------------------------------------	--------------------------	-------------