



DATA SHEET	53111600
SKINTOP® BS-M / BSR-M	valid from : 22.09.2010

SKINTOP® BS-M / BSR-M with polyamide spiral strain relief, is particularly used for flexible cables a handheld equipment, moving machine parts and in many applications of the instrument industry. SKINTOP BS-M / BSR-M with spiral afford protection against conductor damage.



The gland component parts:

Gland body with lamellar design	plastic polyamide-based
Cap nut with spiral	plastic polyamide-based
Seal insert	CR/NBR

Technical features:

Connecting thread:	M 12x1.5 up to M 32x1.5 in acc, to EN 60423
Functional thread:	multi-start trapezoidal thread
IP protection:	IP 68 - 5 bar/ 30 min, test in accordance to EN 60 529
Strain relief:	cat. A to EN 50262
Temperature range:	- 20°C up to + 100°C
Flame rating:	in acc. to UL 94 V2
Type:	BS-M = standard BSR-M = standard with reducing seal insert

Approval:



SKINTOP BSR-M without VDE and DNV approval

For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: PDP: M. Dengler	Document: DB53111600_5EN	page 1 of 1
-----------------------------------	--------------------------	-------------