

Product Description

Adjustable for all wrench sizes ranging from 14 to 33 mm; Assembling after the cables are already inserted; Ergonomic plastic grips



Application range

- For quick mounting of cable and conduit glands

Benefits

- Adjustable for all wrench sizes ranging from 14 to 33 mm
- Assembling after the cables are already inserted
- Ergonomic plastic grips

Product features

- Made of chromium-plated tool steel
- With two expandable clamping ranges (lock positions)
- Small opening (14 - 22 mm): M12 to M16, PG7 to PG11, NPT 3/8"
- Large opening (24 - 33 mm): M20 to M25, PG13.5 to PG21, NPT 1/2" to 3/4"

Article List

Part number	Article designation / size	Width of flat surface (mm)	Overall length (mm)	Pieces / PU
SKINMATIC® RZ				
61791260	SKINMATIC® RZ	14 - 33	250.0	1

Footnote:

Not subjected to RoHS directive.



Photographs are not to scale and do not represent detailed images of the respective products.