


SPECIFICATION FOR APPROVAL


TO:

PART NAME	EMI FILTER	SAMPLE NO	FTB-0707
MODEL	YD05T4	SAMPLE DATE	AUG.23.2004
USED NO		OUR DRAWING NO	YDR-00058a

1. PHYSICAL DIMENSIONS:(mm)



2. SCHEMATIC:



REPORTED BY	CHECKED BY	APPROVED BY	3
	<i>[Signature]</i>		2
王强省 9.10			REV. 1
			更新安規號碼

SPECIFICATION FOR APPROVAL

TO:

PART NAME	EMI FILTER	SAMPLE NO	FTB-0707
MODEL	YD05T4	SAMPLE DATE	AUG.23.2004
USED NO		OUR DRAWING NO	YDR-00058a

3. ELECTRICAL CHARACTERISTICS:

- 3-1. RATED VOLTAGE 125/250VAC
- 3-2. RATED CURRENT 5 A
- 3-3. OPERATING FREQUENCY 50/60Hz
- 3-4. LEAK CURRENT: EACH LINE TO GROUND
250VAC 50Hz 0.8mA MAX
- 3-5. HIPOT RATING: (FOR ONE MINUTE)
LINE TO LINE 1450VDC
LINE TO GROUND 1800VAC
- 3-6. INSULATION RESISTANCE 250VDC/100MOHM MIN
- 3-7. DIRECT CURRENT RESISTANCE 0.3 OHM MAX
- 3-8. OPERATING TEMPERATURE -25 TO +85°C

4. SAFETY COMPLIANCE:

UL FILE NO: E134751
 CSA FILE NO: LR95210
 VDE FILE NO: 40008205