


SPECIFICATION FOR APPROVAL


TO:

PART NAME	EMI FILTER	SAMPLE NO	FTB-0926
MODEL	YE05T4L2	SAMPLE DATE	AUG.23.2004
USED NO		OUR DRAWING NO	YDR-00103a

1. PHYSICAL DIMENSIONS:(mm)



2. SCHEMATIC:



CX : 0.1uF
 CY : 3300pF
 R : 10M Ω
 L : 4 x 5mH

REPORTED BY	CHECKED BY	APPROVED BY	3	
	<i>[Signature]</i>		2	
王强省 4.4.0	<i>[Signature]</i>		REV. 1	更新安规號碼

SPECIFICATION FOR APPROVAL

TO:

PART NAME	EMI FILTER	SAMPLE NO	FTB-0926
MODEL	YE05T4L2	SAMPLE DATE	AUG.23.2004
USED NO		OUR DRAWING NO	YDR-00103a

3.ELECTRICAL CHARACTERISTICS:

- 3-1.RATED VOLTAGE 125/250VAC
- 3-2.RATED CURRENT 5 A
- 3-3.OPERATING FREQUENCY 50/60Hz
- 3-4.LEAK CURRENT: EACH LINE TO GROUND
 250VAC 50Hz 0.8mA MAX
- 3-5.HIPOT RATING:(FOR ONE MINUTE)
 LINE TO LINE 1450VDC
 LINE TO GROUND 1800VAC
- 3-6.INSULATION RESISTANCE 250VDC/100MOHM MIN
- 3-7.DIRECT CURRENT RESISTANCE 0.3 OHM MAX
- 3-8.OPERATING TEMPERATURE -25 TO +85°C

4.SAFETY COMPLIANCE:

UL FILE NO:E134751
 CSA FILE NO:LR95210
 VDE FILE NO:40008205