


SPECIFICATION FOR APPROVAL


TO:

PART NAME	EMI FILTER	SAMPLE NO	FTB-0746
MODEL	YK01T1	SAMPLE DATE	MAR.17.2006
USED NO		OUR DRAWING NO	YDR-00073b

1. PHYSICAL DIMENSIONS:(mm)



2. SCHEMATIC:



REPORTED BY	CHECKED BY	APPROVED BY	3	
王强省	<div style="border: 1px solid black; border-radius: 50%; padding: 5px; display: inline-block;"> 主任 13.17 林宏彦 </div>		2	原44MAX變更44±0.2
			REV. 1	更新安規號碼

SPECIFICATION FOR APPROVAL

TO:

PART NAME	EMI FILTER	SAMPLE NO	FTB-0746
MODEL	YK01T1	SAMPLE DATE	MAR.17.2006
USED NO		OUR DRAWING NO	YDR-00073b

3. ELECTRICAL CHARACTERISTICS:

- 3-1. RATED VOLTAGE 125/250VAC
- 3-2. RATED CURRENT 1 A
- 3-3. OPERATING FREQUENCY 50/60Hz
- 3-4. LEAK CURRENT: EACH LINE TO GROUND
 250VAC 50Hz 0.8mA MAX
- 3-5. HIPOT RATING: (FOR ONE MINUTE)
 LINE TO LINE 1450VDC
 LINE TO GROUND 1800VAC
- 3-6. INSULATION RESISTANCE 250VDC/100MOHM MIN
- 3-7. DIRECT CURRENT RESISTANCE 0.5 OHM MAX
- 3-8. OPERATING TEMPERATURE -25 TO +85°C

4. SAFETY COMPLIANCE:

UL FILE NO: E134751
 CSA FILE NO: LR95210
 VDE FILE NO: 40007880