

Product Description

Halogen-free;Extremely flame-retardant according to UL 94V-0;Self-extinguishing, no dripping



Application range

- For locking SKINTOP® cable glands in boreholes without thread.
- Airports
- Tunnel construction
- Underground railways
- Public buildings

Benefits

- Halogen-free
- Extremely flame-retardant according to UL 94V-0
- Self-extinguishing, no dripping

Design

- Metric connection thread acc. to EN 50262

Note

- Designed for use with SKINTOP® ST-HF-M



Technical Data

Colour delivered

Light grey (RAL 7035)

Material

Polyamide UL 94V-0 - halogen-free

Temperature range

-20°C to +100°C

Article List

Part number	Article designation / size	SW (mm)	PU
SKINTOP® GMP-HF-M			
53119200	12 x 1,5	17	100
53119210	16 x 1,5	22	100
53119220	20 x 1,5	27	100
53119230	25 x 1,5	34	100
53119240	32 x 1,5	41	100
53119250	40 x 1,5	50	25
53119260	50 x 1,5	60	25
53119270	63 x 1,5	75	25

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.