

## Product Description

For closing pre-threaded holes; High stability due to glass fibre reinforcement



## Application range

- Control cabinet manufacturing
- Distribution box
- Junction boxes

## Benefits

- For closing pre-threaded holes
- High stability due to glass fibre reinforcement

## Design

- Metric connection thread acc. to EN 50262



Technical Data

Colour delivered

Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005)

Material

Polyamide, glass fibre-reinforced

Protection rating

IP 54 IP 68 with O-ring

Temperature range

-40°C to +100°C

Article List

Part number	Article designation / size	Thread length/ D (mm)	Pieces / PU
SKINDICHT® BLK-GL-M silver-grey			
52006101	12 x 1,5	6.0	100
52006111	16 x 1,5	6.0	100
52006121	20 x 1,5	6.0	100
52006131	25 x 1,5	8.0	100
52006141	32 x 1,5	8.0	50
52006151	40 x 1,5	8.0	25
52006161	50 x 1,5	10.0	25
52006171	63 x 1,5	12.0	25
SKINDICHT® BLK-GL-M light grey			
52006100	12 x 1,5	6.0	100
52006110	16 x 1,5	6.0	100
52006120	20 x 1,5	6.0	100
52006130	25 x 1,5	8.0	100
52006140	32 x 1,5	8.0	50
52006150	40 x 1,5	8.0	25
52006160	50 x 1,5	10.0	25
52006170	63 x 1,5	12.0	25
SKINDICHT® BLK-GL-M black			
52006103	12 x 1,5	6.0	100
52006113	16 x 1,5	6.0	100
52006123	20 x 1,5	6.0	100
52006133	25 x 1,5	8.0	100
52006143	32 x 1,5	8.0	50
52006153	40 x 1,5	8.0	25
52006163	50 x 1,5	10.0	25



52006173	63 x 1,5	12.0	25
SKINDICHT® BLK-GL-M silver-grey mounted with O-ring			
52006109	12 x 1,5	6.0	100
52006119	16 x 1,5	6.0	100
52006129	20 x 1,5	6.0	100
52006139	25 x 1,5	8.0	100
52006149	32 x 1,5	8.0	50
52006159	40 x 1,5	8.0	25
52006169	50 x 1,5	10.0	25
52006179	63 x 1,5	12.0	25
SKINDICHT® BLK-GL-M light grey mounted with O-ring			
52006107	12 x 1,5	6.0	100
52006117	16 x 1,5	6.0	100
52006127	20 x 1,5	6.0	100
52006137	25 x 1,5	8.0	100
52006147	32 x 1,5	8.0	50
52006157	40 x 1,5	8.0	25
52006167	50 x 1,5	10.0	25
52006177	63 x 1,5	12.0	25
SKINDICHT® BLK-GL-M black mounted with O-ring			
52006106	12 x 1,5	6.0	100
52006116	16 x 1,5	6.0	100
52006126	20 x 1,5	6.0	100
52006136	25 x 1,5	8.0	100
52006146	32 x 1,5	8.0	50
52006156	40 x 1,5	8.0	25
52006166	50 x 1,5	10.0	25
52006176	63 x 1,5	12.0	25

**Footnote:**

Photographs are not to scale and do not represent detailed images of the respective products.