

Product Description

For the benefits, refer to SKINTOP® ST-M



Application range

- With reducing seal insert, to seal cables with smaller outer diameters.

Benefits

- For the benefits, refer to SKINTOP® ST-M

Design

- Metric connection thread acc. to EN 50262

Approvals

- UL File Nr. E79903

Note

- Refer to SKINTOP® metric accessories for suitable accessories
- Counter nut to be used: SKINTOP® GMP-GL-M
- SKINTOP® STR M ISO types have an extra-long connection thread
- SKINTOP® STR M ISO versions with extra-long connection thread, see table, no DNV approval



Technical Data

Caution

Refer to Appendix T21 for the installation dimensions and torques

Colour delivered

Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant

Material

Body: Polyamide Seal: CR

Tests

GGVS: TÜ.EGG.020-95

Protection rating

IP 68 - 5 bar

IP 69 K

Temperature range

Fixed: -40°C to +100°C

Dynamic: -20°C to +80°C

Article List

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINTOP® STR-M silver grey						
53111100	STR-M 12 x 1,5	1-5	15	30.0	8.0	100
53111110	STR-M 16 x 1,5	2-7	19	34.0	8.0	100
53111120	STR-M 20 x 1,5	5-10	25	37.0	9.0	100
53111130	STR-M 25 x 1,5	6-13	30	40.0	10.0	50
53111140	STR-M 32 x 1,5	7-15	36	47.0	10.0	25
53111150	STR-M 40 x 1,5	15-23	46	52.0	10.0	10
53111160	STR-M 50 x 1,5	22-29	55	62.0	12.0	5
53111170	STR-M 63 x 1,5	28-39	66	71.0	12.0	5
SKINTOP® STR-M black						
53111300	STR-M 12 x 1,5	1-5	15	30.0	8.0	100
53111310	STR-M 16 x 1,5	2-7	19	34.0	8.0	100
53111320	STR-M 20 x 1,5	5-10	25	37.0	9.0	100
53111330	STR-M 25 x 1,5	6-13	30	40.0	10.0	50
53111340	STR-M 32 x 1,5	7-15	36	47.0	10.0	25
53111350	STR-M 40 x 1,5	15-23	46	52.0	10.0	10
53111360	STR-M 50 x 1,5	22-29	55	62.0	12.0	5
53111370	STR-M 63 x 1,5	28-39	66	71.0	12.0	5
SKINTOP® STR-M light grey						
53111500	STR-M 12 x 1,5	1-5	15	30.0	8.0	100
53111510	STR-M 16 x 1,5	2-7	19	34.0	8.0	100
53111520	STR-M 20 x 1,5	5-10	25	37.0	9.0	100



53111530	STR-M 25 x 1,5	6-13	30	40.0	10.0	50
53111540	STR-M 32 x 1,5	7-15	36	47.0	10.0	25
53111550	STR-M 40 x 1,5	15-23	46	52.0	10.0	10
53111560	STR-M 50 x 1,5	22-29	55	62.0	12.0	5
53111570	STR-M 63 x 1,5	28-39	66	71.0	12.0	5
SKINTOP® STR M ISO silver-grey (with long metric connecting thread)						
53017110	STR M 16 x 1,5	2-6	19	40.0	12.0	100
53017130	STR M 20 x 1,5	4-9	24	45.0	13.0	100
53017140	STR M 25 x 1,5	6-12	27	47.0	13.0	50
SKINTOP® STR M ISO black (with long metric connecting thread)						
53017310	STR M 16 x 1,5	2-6	19	40.0	12.0	100
53017330	STR M 20 x 1,5	4-9	24	45.0	13.0	100
53017340	STR M 25 x 1,5	6-12	27	47.0	13.0	50

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.