





**4-CONDUCTOR TERMINAL STRIP
LATERAL MARKING WITH SNAP-IN
MOUNTING FOOT**
260-252 TO 260-262

ITEM-NO. (ITEM-NO.)	260-256
Cross section1 (Cross section / mm²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 16
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	400
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	18
P (NO. OF POLES)	6
Height (Height / mm)	17
Width (Width / mm)	52.4
Depth (Depth / mm)	25
No. of connection Points (No. of connection Points)	24
No. of potentials (No. of potentials)	6
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	16.18
Comment (Comment)	L = (No. of poles x pole width) + 4,4 mm