



ITEM-NO. (ITEM-NO.)	261-202/332-000
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	500
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	24
P (NO. OF POLES)	2
Height (Height / mm)	23.2
Width (Width / mm)	34.5
Depth (Depth / mm)	28
No. of connection Points (No. of connection Points)	8
No. of potentials (No. of potentials)	4
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	9.748
Comment (Comment)	L = (No. of poles x pole width) L1 = L + 8,1 mm L2 = L + 14,5 mm