



| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 261-210/332-000 |
| Cross section1 (Cross section / mm²) | 0.08 - 2.5 |
| Cross section2 (Cross section / AWG) | 28 - 14 |
| Strip length (Strip length / mm) | 8 - 9 |
| Measured voltage (Measured voltage / V) | 500 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 24 |
| P (NO. OF POLES) | 10 |
| Height (Height / mm) | 23.2 |
| Width (Width / mm) | 114.5 |
| Depth (Depth / mm) | 28 |
| No. of connection Points (No. of connection Points) | 40 |
| No. of potentials (No. of potentials) | 20 |
| COLOR (COLOR) | grau |
| WEIGHT (WEIGHT / g) | |
| Comment (Comment) | L = (No. of poles x pole width) L1 = L + 8,1 mm L2 = L + 14,5 mm |