

PVC NET HOSE

Features:

Light weight and flexible. Good transparent Smoothness of internal lessens fluid-resistance.

Applications:

For various machine tools, and transportation of chemicals. Civil engineering and construction.

Notes on use:

1. Adaptable temperature for continued application: $-10^{\circ}\text{C} \sim 65^{\circ}\text{C}$.
2. Bursting pressure indicated is more than five times as much as working pressure.
3. Minimum bending radius is five times as much as its ID.

Specifications:

Size	I.D. x O.D. (mm/mm)	Length (Mtr)	Working pressure	Bursting pressure
3/16"	4.8 x 9.8	100	10 kg/m ²	70 kg/m ²
1/4"	6.4 x 11.4	100	10	55
5/16"	8.0 x 13.0	100	8	40
3/8"	9.5 x 14.5	100	8	40
1/2"	12.7 x 17.7	100	7	35
5/8"	15.9 x 20.9	50.100	7	35
3/4"	19.1 x 25.1	50.100	5	25
1"	25.4 x 32.4	50	5	25
1-1/4"	32.0 x 40.0	40	3	15
1-1/2"	38.1 x 47.1	40	3	15
2"	50.8 x 60.8	40	2	10

