



ITEM-NO. (ITEM-NO.)	261-317/341-000
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	
Measured shock voltage (Measured shock voltage / kV)	
Pollution degree (Pollution degree)	
Current intensity (Current intensity / A)	
Height (Height / mm)	23.2
Width (Width / mm)	6
Depth (Depth / mm)	28
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	1
COLOR (COLOR)	grün-gelb
WEIGHT (WEIGHT / g)	2.524