

Klippon KLIPPON K4 EX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



For many years, the name Klippon® has stood for competence and quality in enclosures. The enclosures are ideal for turnkey customised solutions for standard industrial applications and for explosive-risk applications.

Improved products that meet all application requirements: this was Weidmüller's aim during the update of the Klippon® K housing series. Weidmüller delivers many types of aluminium enclosures; they are designed to fit precisely with a wide range of customer requirements and applications.

Our comprehensive product line provides the following advantages:

- Available in two different surfaces: natural and powder-coated (RAL 7001)
- Available normally with silicone or chloroprene gasket seal
- A uniform Torx-slotted screw head is used for over 19 different housing sizes.
- Mounting holes not within the sealed area
- High degree of protection: IP66, IP67 and IP68
- Impact resistance of up to 10 Joules
- The housings are certified by ATEX, GOST, GOST Ex, cULus, Russian Maritime Register, German Lloyd, as well as the empty housing standard.
- Alloy is resistant to salt water

- Standardised distributor housings with threaded holes and a variety of terminal configurations

General ordering data

Order No.	9526910000
Type	KLIPPON K4 EX
Version	Enclosures, Aluminium AlSi12, 82 mm, 72 mm, 130 mm
GTIN (EAN)	4032248019083
Qty.	1 pc(s).

**Klippon
KLIPPON K4 EX**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	72 mm	Width	130 mm
Height	82 mm	Mounting dimension - width	116 mm
Mounting dimension - height	68 mm	Weight	620 g
Net weight	663 g		

Cable glands, left

M12 (3)	2	M16 (3)	2
M20 (3)	1	M25 (3)	1
M32 (3)	1		

Cable glands, right

M12 (2)	2	M16 (2)	2
M20 (2)	1	M25 (2)	1
M32 (2)	1	Side of enclosure	left, right

Cable glands, top/bottom

M12	5	M16	3
M20	2	M25	2
Side of enclosure	left, right		

General information

Areas of use	Explosive risk zone, Process industry, Transportation, Packaging industry, Marine engineering, Machine construction, Harbour facilities	Torque for cover screws	2.5 Nm
Material	Aluminium AISi12	Seal material	Silicone
Surface finish	untreated	Operating temperature, min.	-30 °C
Operating temperature, max.	80 °C	Impact resistance	7.00 J
Protection degree	IP 66, IP 67	Enclosure attachment	Holes 5 mm
Cover attachment	M4 torx stainless steel screws with slot	Integral fixing	Threaded holes M5

horizontal assembly

WDU 2,5 / ZDU 2,5 / IDU 2,5	*	WDU 4 / ZDU 4	*
-----------------------------	---	---------------	---

vertical assembly

WDU 10 / ZDU 10 (2)	1x2	WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	1x5
WDU 4 / ZDU 4 (2)	1x4	WDU 6 / ZDU 6 (2)	1x3

Classifications

ETIM 2.0	EC000520	ETIM 3.0	EC000049
UNSPSC	31-26-15-02	eClass 4.1	27-14-12-06
eClass 5.1	27-18-05-02	eClass 6.0	27-18-05-02
eClass 7.0	27-18-05-02		

Data sheet...**Klippon
KLIPPON K4 EX**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Test certificates**

Certificate No. (ATEX)	KEMA00ATEX8501X	Certificate No. (GERMLLOYD)	44536-07
Certificate No. (MARITREG)	09.04040.250		


Approvals

Approvals



**Klippon
KLIPPON K4 EX**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

**Klippon
KLIPPON K4 EX**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Accessories**64 mm (K4)**

Mounting rails are available in widths of 15 and 35 mm. They are cut to fit the various housing sizes. Three mounting plates are also available as an alternative to the mounting rail for small and flat housings.

General ordering data

Order No.	Type	Version	GTIN (EAN)	Qty.
1910060000	TS35 64 Klippon K4K11	Mounting rail, 64 mm	4032248536979	1 pc(s).