



Core: 26x14,5x20 μ i=6000
 Wire: 1,4 W210 GRD2
 Tin: S-Sn 99,9% (EN-610)
 Cap: H-384
 Winding turns: 10



scale 1 : 1

ELECTRICAL REQUIREMENTS:

ITEM	UNIT	TEST FREQUENCY	TEST INSTRUMENT
L	1mH +50% / -20%	1kHz (50mV)	:HP 4194A
R _{DC}	< 7,5mOhm		:HIOKI 3540
I _{DC}	16 A		

Issue	0					ISO		
Date	10.02.10					METRIC		
Date	Rev.	Remarks				Dimension in mm.	Scale: 1,5 : 1	Part Name:
10.02.10	0	New drawing				Drawn by:		Approved by:
						Checked by:	Approved by:	Part Number:
								534455
								Valid when no tolerance is given:
								>=0.2 >=0.5 >=3 >=6 >=30 >=120 < 0.5 < 2 < 6 < 18 < 120 < 120 ±0.1 ±0.1 ±0.1 ±0.2 ±0.3 ±0.5
								Radius and chamfer
								±0.1 ±0.2 ±0.5 ±1 ±2 ±4