



|   |           |
|---|-----------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 262-307   |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.08 - 4  |
| <b>Cross section2 (Cross section / AWG)</b>                 | 28 - 12   |
| <b>Strip length (Strip length / mm)</b>                     | 9 - 10    |
| <b>Measured voltage (Measured voltage / V)</b>              |           |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> |           |
| <b>Pollution degree (Pollution degree)</b>                  |           |
| <b>Current intensity (Current intensity / A)</b>            |           |
| <b>Height (Height / mm)</b>                                 | 23        |
| <b>Width (Width / mm)</b>                                   | 7         |
| <b>Depth (Depth / mm)</b>                                   | 33.5      |
| <b>No. of connection Points (No. of connection Points)</b>  | 2         |
| <b>No. of potentials (No. of potentials)</b>                | 1         |
| <b>COLOR (COLOR)</b>  | grün-gelb |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 4.13      |