





**2-CONDUCTOR TERMINAL BLOCK
LATERAL MARKING WITH SNAP-IN
MOUNTING FOOT
262-311**

ITEM-NO. (ITEM-NO.)	262-317
Cross section1 (Cross section / mm²)	0.08 - 4
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	
Measured shock voltage (Measured shock voltage / kV)	
Pollution degree (Pollution degree)	
Current intensity (Current intensity / A)	
Height (Height / mm)	23
Width (Width / mm)	7
Depth (Depth / mm)	33.5
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	1
COLOR (COLOR)	grün-gelb
WEIGHT (WEIGHT / g)	4.2