



ITEM-NO. (ITEM-NO.)	264-104
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	800
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	24
P (NO. OF POLES)	4
Height (Height / mm)	22
Width (Width / mm)	40
Depth (Depth / mm)	32
No. of connection Points (No. of connection Points)	8
No. of potentials (No. of potentials)	4
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	17.4
Comment (Comment)	L = (No. of poles x pole width) L1 = L + 9,6 mm L2 = L + 16 mm