





2-CONDUCTOR TERMINAL STRIP CENTRE MARKING WITH SNAP-IN MOUNTING FOOT 264-152 TO 264-162

ITEM-NO. (ITEM-NO.)	264-190
Cross section1 (Cross section / mm²)	0.5 - 2.5
Cross section2 (Cross section / AWG)	20 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	690
Measured shock voltage (Measured shock voltage / kV)	
Pollution degree (Pollution degree)	
Current intensity (Current intensity / A)	23
P (NO. OF POLES)	10
Height (Height / mm)	22
Width (Width / mm)	67
Depth (Depth / mm)	32
No. of connection Points (No. of connection Points)	20
No. of potentials (No. of potentials)	10
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	41.9
Comment (Comment)	L = (No. of poles x pole width)