



| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 264-240 |
| Cross section1 (Cross section / mm²) | 0.5 - 2.5 |
| Cross section2 (Cross section / AWG) | 20 - 12 |
| Strip length (Strip length / mm) | 8 - 9 |
| Measured voltage (Measured voltage / V) | 690 |
| Measured shock voltage (Measured shock voltage / kV) | |
| Pollution degree (Pollution degree) | |
| Current intensity (Current intensity / A) | 23 |
| P (NO. OF POLES) | 10 |
| Height (Height / mm) | 22.1 |
| Width (Width / mm) | 116 |
| Depth (Depth / mm) | 32 |
| No. of connection Points (No. of connection Points) | 40 |
| No. of potentials (No. of potentials) | 10 |
| COLOR (COLOR) | lichtgrau |
| WEIGHT (WEIGHT / g) | 70.9 |
| Comment (Comment) | L = (No. of poles x pole width) L1 = L + 9,6 mm L2 = L + 16 mm |