





**4-CONDUCTOR MINIATURE
THROUGH TERMINAL BLOCK
CENTRE MARKING for DIN 35 rail
264-731**

ITEM-NO. (ITEM-NO.)	264-736
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	800
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	24
Height (Height / mm)	24.5
Width (Width / mm)	10
Depth (Depth / mm)	38
No. of connection Points (No. of connection Points)	4
No. of potentials (No. of potentials)	1
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	6.088
Comment (Comment)	